

perfect®

Endo Motor

MR-Auto-Motor



Motor+Apex



Outstanding
LCD Display



Swiss Motor



Durable Battery



Root Canal
Treatment

perfect®

MR-Auto-Motor



Shenzhen Perfect Medical Instruments Co., Ltd.
Add 1F,Bldg.C.plant. No.3, Jixia Zaohekeng Industrial Zone,
Nanwan St., Longgang Dist., Shenzhen, China
TEL:+86(755) 28540953
FAX:+86(755) 28540953
Website: www.dental-perfect.com



MR-Auto-Motor



MOTOR+APEX



Low power consumption; Standby consumption is only 0.05W, normal OLED is workable with 0.25W~0.42W.



Longer standby for 140h and Continuous use for at least 70h.



Multi-frequency detection technology, accurately measure the root canal length. (Independently developed multi-frequency without frequency division, ensuring the measurement results of each device are precise.




Self-developed DC drive, more stable of motor speed (300rpm no-load operation power consumption is only 0.16W. compare to traditional PWM drive mode, 300rpm consumption is generally above 0.8W).




Stepped pen segment display, the closer to apex, the more accurate data display.



FSTN LCD super clear display.




Lightweight handle (only 100g).




10 adjustable modes.CW CCW REC ATC, measurement.



150-600rpm Speed, 0.6-4.0N.cm Torque.



Reciprocating rotation angle F170°R50°, F30°R150°, F50°R170°.



1500mAh Large capacity battery.

PERFECT Endo.



Individual P0 Apex Location.



P1~P9 real time display the movement of root canal files. (The root canal length is preset. Preset range is 0-1.0, Automatically reverses when the file reaches the setting value).

